



# S1928

LU1000/ET25  
1000 watt; High Pressure Sodium HID; Mogul base; ET25;  
Clear; 22 CRI; 2100K

### Features

- High Efficacy
- Long Life
- Universal operating position



S1928

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S1928	045923019289	1000	ET25	Mogul	E39	S52	LU1000/ET25

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	15.06"	3.13"	24000	130000	2100	12	22

Burning Position	RoHS Compliant
Universal	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S1928

LU1000/ET25  
1000 watt; High Pressure Sodium HID; Mogul base; ET25;  
Clear; 22 CRI; 2100K

### Features

- High Efficacy
- Long Life
- Universal operating position



S1928

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S1928	045923019289	1000	ET25	Mogul	E39	S52	LU1000/ET25

Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	15.06"	3.13"	24000	130000	2100	12	22

Burning Position	RoHS Compliant
Universal	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

