

Eaton S20N11P01P

Catalog Number: S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A

General specifications



Photo is representative

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton General purpose encapsulated transformer | S20N11P01P |
| | UPC |
| | 786680073687 |
| Product Length/Depth | Product Height |
| 6.56 in | 13.03 in |
| Product Width | Product Weight |
| 5.53 in | 25 lb |
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

67P

Insulation

180 °C

Mounting

Wall

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

3A

Miscellaneous

Weathershield

Indoor-Outdoor

Performance Ratings

Frequency rating

60 Hz

Kva Rating

1 kVA

kVA

1 kVA

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

1 kVA

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S20N11P01P



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)