



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S20N11P16P 1.5KVA Type Ep Transformer 1PH 240X480-120/240V

Eaton Corp

Catalog Number	S20N11P16P
Manufacturer	Eaton Corp
Description	Eaton, General Purpose Encapsulated Transformer, Ep, Single-Phase, PV: 240 X 480V, Taps: None, SV: 120/240V, 115°C, 1.5 Kva, Al Windings, Frame: 67P, Indoor-Outdoor
Weight per unit	32.4 (lbs/each)
Product Category	Single Phase Non Ventilated to

### Features

design	EP
dimensions	6.5600 IN X 5.5300 IN X 13.0300 IN
kva rating	1.5 kVA
Number of Phases	Single-phase
Tap Size	NONE

### Descriptions

Description	1.5KVA TYPE EP TRANSFORMER 1PH 240X480-120/240V
extra long description	ETN S20N11P16P 1.5KVA TYPE EP XFMR
Features	Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA.
Long Description	Eaton, general purpose encapsulated transformer, ep, single-phase, pv: 240 x 480v, taps: none, sv: 120/240v, 115°C, 1.5 kva, al windings, frame: 67p, indoor-outdoor
Product Type	1.5KVA Type Ep XFMR 1PH 240X480-120/240V

### Manufacturer Information

Brand	Eaton
GTIN	00786680073717
Manufacturers Part Number	S20N11P16P
UPC	786680073717

### Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Encapsulated transformer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	32.35

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Frequency Rating	60 Hz
standard	UL Listed
Temperature Rating	115 °C rise