



OLD WORK SWITCH & OUTLET BOX WITH QUICK/CLICK

S232W | [Pass & Seymour](#)

FEATURES & BENEFITS

Double Gang, Old Work Switch and Outlet box with swing-bracket for mounting, adjusts from 1 1/4" to 1/8". It has four Auto/Clamps for each end. It has a durable, impact-resistant thermoplastic box. The metal swing bracket is for quick mounting in existing walls. 50 pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 4 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Type: Switch, Outlet Box

Special Features: Old Work, Quick/Click

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes
UN SPSC: 39121308
UR: No

DIMENSIONS

Depth (US): 3.03125
Length (US): 3.75
Width (US): 4.0625
Volume: 32.0

TECHNICAL INFORMATION

Material: Plastic

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant





OLD WORK SWITCH & OUTLET BOX WITH QUICK/CLICK

S232W | [Pass & Seymour](#)

FEATURES & BENEFITS

Double Gang, Old Work Switch and Outlet box with swing-bracket for mounting, adjusts from 1 1/4" to 1/8". It has four Auto/Clamps for each end. It has a durable, impact-resistant thermoplastic box. The metal swing bracket is for quick mounting in existing walls. 50 pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 4 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater
Type: Switch, Outlet Box
Special Features: Old Work, Quick/Click

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No

UL Listing No: Yes
UN SPSC: 39121308
UR: No

DIMENSIONS

Depth (US): 3.03125
Length (US): 3.75
Width (US): 4.0625
Volume: 32.0

TECHNICAL INFORMATION

Material: Plastic

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

