



S2414

40ST19/CL /9S /120V /Vintage
40 watt ST19 Incandescent; Clear; 3000 average rated hours;
160 lumens; Medium base; 120 volts

Features

- Vintage Style incandescent
- Historic restoration quality
- Classic, warm glow



S2414

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S2414	045923024146	40	ST19	Medium	E26	40ST19/CL /9S /120V /Vintage	120

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Clear	5 3/16"	2.38"	Hairpin	160	3000	48/6	Box

RoHS Compliant
Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

