



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S28684 4W Led E11 Mini 30K Clear Candelabra Base 120-130V

Satco

| | |
|------------------|--|
| Catalog Number | S28684 |
| Manufacturer | Satco |
| Description | Led Lamp, Dimmable Type; 2-3/8 Inch; Ul, Etl (Canada and Us), Cec Approval; 120 to 130 Volt Ac 50/60 Hertz Voltage Rating; 1/2 Inch Diameter; 4 Watt Wattage; Led Lamp; E11 Mini Candelabra Base Type; 25000 Life In Hour; 480 Lumen Intensity; 3000 |
| Weight per unit | 0.0300 (lbs/each) |
| Product Category | Led Specialty Lamps & Modules |

Features

| | |
|-------------------|--------------------------------|
| Beam Spread Angle | 360 Degree |
| Glass Finish | CLEAR |
| Intensity | 480 LUMEN |
| Item | LED Lamp |
| Voltage Rating | 120 to 130 Volt AC 50/60 Hertz |
| Wattage | 4 Watt |

Material, Color, and Finish

| | |
|-----------------------------|---------------------|
| Base Type | E11 Mini Candelabra |
| Color Rendering Index | 80 A |
| Color Temperature in Kelvin | 3000 |
| Glass Color | WARM WHITE |

Dimensions and Weight

| | |
|----------|------------|
| Diameter | 1/2 INCH |
| Length | 2-3/8 INCH |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Additional Information | RoHS Compliant |
| Commodity Description | LED SPECIALTY LAMPS & MODULES |
| Description | 4W LED E11 MINI 30K CLEAR CANDELABRA BASE 120-130V |
| extra long description | DIMMABLE TYPE; 2-3/8 INCH; UL, ETL (CANADA AND US), CEC APPROVAL; 120 TO 130 VOLT AC 50/60 HERTZ VOLTAGE RATING; 1/2 INCH DIAMETER; 4 WATT WATTAGE; LED LAMP; E11 MINI CANDELABRA BASE TYPE; 25000 LIFE IN HOUR; 480 LUMEN INTENSITY; 3000; 80 COLOR RENDERING INDEX; CLEAR GLASS FINISH; WARM WHITE GLASS COLOR; 360 DEGREE BEAM SPREAD ANGLE; OMNI-DIRECTIONAL BEAM SPREAD TYPE; ROHS COMPLIANT |
| Long Description | LED LAMP, DIMMABLE TYPE; 2-3/8 INCH; UL, ETL (CANADA AND US), CEC APPROVAL; 120 TO 130 VOLT AC 50/60 HERTZ VOLTAGE RATING; 1/2 INCH DIAMETER; 4 WATT WATTAGE; LED LAMP; E11 MINI CANDELABRA BASE TYPE; 25000 LIFE IN HOUR; 480 LUMEN INTENSITY; 3000 |
| Product Type | Led Lamp |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923286841 |
| Manufacturers Part Number | S28684 |
| UPC | 045923286841 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | LED SPECIALTY LAMPS & MODULES |
| Type | DIMMABLE |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.03 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------------|
| Approval | UL, ETL (Canada and US), CEC |
| Energy Star | yes |