



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29454 15W Led PAR38 5000K 80 Cri 60 Deg 1200LM

Satco

Catalog Number	S29454
Manufacturer	Satco
Description	15 Watt PAR38 Led Lamp - 5000K - 60 Degree Beam Angle - Medium Base - 120 Volts
Weight per unit	0.7900 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	Medium
beam angle	60
lumens	1.2k
Material	Plastic
Shape	PAR38
Warranty	3 Year Limited - 12 hr per day

Material, Color, and Finish

color temperature	5000
Finish	Silver

Dimensions and Weight

Size	5
------	---

Descriptions

Description	15W LED PAR38 5000K 80 CRI 60 DEG 1200LM
extra long description	SATCO S29454 15PAR38/LED/60'/950/12
Long Description	15 Watt PAR38 LED Lamp - 5000K - 60 Degree Beam Angle - Medium Base - 120 Volts
Product Type	15PAR38/Led/60'/950/120V
Special Features	Lawful for sale in California ; Lawful for sale in California ; Yes - Dimmable ; Lens finish: Clear ; Warranty: 3 Year Limited - 12 hours per day ; Wet location rated ; Material: Plastic ; Incandescent Equivalent: 90W ; Enclosed Fixture Rated: Yes ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F)

Manufacturer Information

Brand	Satco
GTIN	00045923294549
Manufacturers Part Number	S29454
UPC	045923294549



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
Type	LED PAR

Packaging

Carton	1
Package	12
Weight	0.34
Weight Per each	0.79

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus