



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29835 9.8WATT A19 Led 27K

Satco

| | |
|------------------|--|
| Catalog Number | S29835 |
| Manufacturer | Satco |
| Description | A19 Led Lamp, 220 ° Beam Angle, 2700 K, 800 LM Brightness (Lumens), 9.8 W, 120 V, Frosted White, 25000 H Average Life, Medium Base, Dimmable, 2.38 In Diameter, 4.17 In Length, 0.98 Power Factor, -4 °F Operating Temperature, +113 °F Operating Temperature, 0.15 LB |
| Weight per unit | 0.1900 (lbs/each) |
| Product Category | Led A-Line A Shape Lamps |

Features

| | |
|----------------|--------------------------------|
| connection | Medium |
| Fixture Type | Type A |
| lumens | 800 |
| Material | Plastic; Metal |
| Shape | A19 |
| Voltage Rating | 120 |
| Warranty | 5 Year Limited - 10 hr per day |

Material, Color, and Finish

| | |
|-------|---------------|
| Color | Frosted White |
|-------|---------------|

Dimensions and Weight

| | |
|------|----------------------|
| Size | MOL: 4.19, MOD: 2.38 |
|------|----------------------|

Descriptions

| | |
|------------------------|---|
| Description | 9.8WATT A19 LED 27K |
| extra long description | SATCO S29835 9.8A19/OMNI/220/LED/27 |
| Special Features | Dimmable: Yes Dimmable ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Power Factor: 0.98 ; Safety Listing: cULus - Damp ; SDS Class: LED_Lamp ; Tested Lumens: 800 |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00045923298356 |
| UPC | 045923298356 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | LED A-LINE SHAPE LAMPS |
| Type | Lamps |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.19 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-----------------------|--|
| Operating Temperature | -25C (-13F) to a maximum of +45C (+113F) |
| standard | cULus - Damp |