

Project Name

Location

Prepared By



## SATCO S39027

9WLED/DW/RDL/5-6/30K/120V

### Notes

[www] 11-22-2021 02:57:43

### General

Status	Active
Wattage	9W
Voltage	120V
Finish	White
CCT (Kelvin)	3000
Color Temperature	Warm White
Lumen Output	620L
Indoor or Outdoor Fixture	Indoor

### Specifications

Technology	LED
CRI	90
Beam Angle	100
Rated Hours	40000
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Dimmable	Yes-Dimmable
IC Rated	Yes

### Dimensions

Width (in.)	6.69
Height (in.)	2.81
Weight (lb.)	0.44

### Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2382278
California Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

### Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------