



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S40590EL00 1/2" SS304 90 Rigid Elbow

Calbrite

| | |
|------------------|---|
| Catalog Number | S40590EL00 |
| Manufacturer | Calbrite |
| Description | Rigid Stainless Steel 304 Elbow 1/2" 90 Degrees |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Steel |

Features

| | |
|------------------|-------|
| Inside Diameter | 0.62 |
| outside diameter | 0.840 |
| Wall Thickness | 0.11 |

Material, Color, and Finish

| | |
|--------|--------------------|
| Color | Polished Silver |
| Finish | #4 Polished Finish |

Dimensions and Weight

| | |
|-------|------|
| Depth | 13.5 |
|-------|------|

Descriptions

| | |
|------------------------|--|
| Description | 1/2" SS304 90 RIGID ELBOW |
| extra long description | CAL S40590EL00 1/2" X 90 Degree SS3 |
| Features | Stainless steel elbows are bent sections of rigid conduit to help in changing the direction of conduit. Available in 90° & 45° elbows and special radii in type 304 and 316SS. |
| Long Description | Rigid Stainless Steel 304 Elbow 1/2" 90 Degrees |
| Product Type | 1/2" X 90 Degree SS304 Elbow |
| Short Description | SS_90ELB_304 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | CALBRITE |
| GTIN | 00847656000370 |
| Manufacturers Part Number | S40590EL00 |
| UPC | 847656000370 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | RIGID ELBOWS |
| Type | Rigid;Rigid Elbow |

Trade Size

| | |
|------------|-----|
| Trade Size | 1/2 |
|------------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight | 0.81 |
| Weight Per each | 1 |

Uses, Certifications, and Standards

| | |
|--------------------|------|
| Temperature Rating | 1600 |
|--------------------|------|