



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S41090EL00 1" SS304 90 Rigid Elbow

Calbrite

| | |
|------------------|---|
| Catalog Number | S41090EL00 |
| Manufacturer | Calbrite |
| Description | Rigid Stainless Steel 304 Elbow 1" 90 Degrees |
| Weight per unit | 2.1 (lbs/each) |
| Product Category | Steel |

Features

| | |
|------------------|-------|
| Inside Diameter | 1.05 |
| outside diameter | 1.315 |
| Wall Thickness | 0.132 |

Material, Color, and Finish

| | |
|--------|--------------------|
| Color | Polished Silver |
| Finish | #4 Polished Finish |

Dimensions and Weight

| | |
|-------|----|
| Depth | 17 |
|-------|----|

Descriptions

| | |
|------------------------|--|
| Description | 1" SS304 90 RIGID ELBOW |
| extra long description | CAL S41090EL00 1" X 90 Degree SS304 |
| Features | Stainless steel elbows are bent sections of rigid conduit to help in changing the direction of conduit. Available in 90° & 45° elbows and special radii in type 304 and 316SS. |
| Long Description | Rigid Stainless Steel 304 Elbow 1" 90 Degrees |
| Product Type | 1" X 90 Degree SS304 Elbow |
| Short Description | SS_90ELB_304 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | CALBRITE |
| GTIN | 00847656000394 |
| Manufacturers Part Number | S41090EL00 |
| UPC | 847656000394 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | RIGID ELBOWS |
| Type | Rigid;Rigid Elbow |

Trade Size

| | |
|------------|---|
| Trade Size | 1 |
|------------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|----------------------|-----------|
| Carton..... | 1..... |
| Weight..... | 2.19..... |
| Weight Per each..... | 2.13..... |

Uses, Certifications, and Standards

| | |
|-------------------------|-----------|
| Temperature Rating..... | 1600..... |
|-------------------------|-----------|