



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S49395 80W Led/Hid 50K Mogul Base

Satco

Catalog Number	S49395
Manufacturer	Satco
Description	80 Watt Led Hid Replacement - 5000K - Extended Mogul Base - Type B Ballast Bypass - Economy Hi-Pro
Weight per unit	3.4 (lbs/each)
Product Category	Lighting

Features

average life	35000
Base	Extended Mogul
beam angle	300
Shape	Corncob

Material, Color, and Finish

Finish	white
--------	-------

Dimensions and Weight

Size	8.69
------	------

Descriptions

Description	80W LED/HID 50K MOGUL BASE
extra long description	SATCO S49395 80W/LED/HP/850/100-277
Long Description	80 Watt LED HID Replacement - 5000K - Extended Mogul Base - Type B Ballast Bypass - Economy Hi-Pro
Product Type	80W/Led/HP/850/100-277V/Ex39
Special Features	Lawful for sale in California ; Lumens: 11040 ; CCT: 5000K ; Color Temperature: Natural Light ; Dimmable: Non-Dimmable ; Lamp Appearance: Clear ; MOL: 8.69 in. ; MOD: 4.72 in. ; Weight: 3.00 lb. ; Warranty: 3 Year Limited ; Brand: Hi-Pro ; Enclosure Rating: Enclosed Rated Lamp ; FCC Compliant: Yes ; Ballasting Requirements: Ballast Bypass ; HID Equivalent: 320W ; Indoor/Outdoor: Indoor and Outdoor ; IP Rating: IP65 ; Lamp Ballast: Type B ; Mounting: Base Up or Base Down Only ; Operating Temperature: -30C (

Manufacturer Information

Brand	Satco
GTIN	00045923493959
Manufacturers Part Number	S49395
UPC	045923493959



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Type Corncob

Packaging

Carton 1

Weight Per each 3.36

Uses, Certifications, and Standards

standard cULus Classified - cULus Listed