



# S4999

250R40/1  
250 watt R40 Incandescent; Clear Heat; 6000 average rated hours; Medium base; 120 volts

### Features

- General Service Reflector
- Household or Commercial use
- Long Life
- Brass Base



S4999

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4999	045923049996	250	R40	Medium	E26	250R40/1	120

Finish	MOL In Inches	MOD In Inches	Filament	Average Rated Hours	Pack	Package Type	RoHS Compliant
Clear Heat	6 1/2"	5.00"	C-9	6000	12	Sleeve	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S4999

250R40/1  
250 watt R40 Incandescent; Clear Heat; 6000 average rated hours; Medium base; 120 volts

### Features

- General Service Reflector
- Household or Commercial use
- Long Life
- Brass Base



S4999

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4999	045923049996	250	R40	Medium	E26	250R40/1	120

Finish	MOL In Inches	MOD In Inches	Filament	Average Rated Hours	Pack	Package Type	RoHS Compliant
Clear Heat	6 1/2"	5.00"	C-9	6000	12	Sleeve	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

