



# S5839

MS250/ED28 /PS /U /4K  
250 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;  
4000K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5839

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5839	045923058394	250	ED28	Mogul	E39	M153/E	MS250/ED28 /PS /U /4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	8.31"	3.50"	15000	25000	4000	Cool White	Yes
Pack	CRI	Burning Position			RoHS Compliant		
12	65	Universal			Yes		



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S5839

MS250/ED28 /PS /U /4K  
250 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;  
4000K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5839

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5839	045923058394	250	ED28	Mogul	E39	M153/E	MS250/ED28 /PS /U /4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	8.31"	3.50"	15000	25000	4000	Cool White	Yes
Pack	CRI	Burning Position			RoHS Compliant		
12	65	Universal			Yes		



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

