



# S5841

MS320/ED28 /PS /U /4K  
320 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;  
4200K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5841

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5841	045923058417	320	ED28	Mogul	E39	M154/E	MS320/ED28 /PS /U /4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	8.31"	3.50"	20000	33000	4200	Cool White	Yes
Pack	Package Type	CRI	Burning Position	RoHS Compliant			
12	Box	65	Universal	Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S5841

MS320/ED28 /PS /U /4K  
320 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;  
4200K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5841

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S5841	045923058417	320	ED28	Mogul	E39	M154/E	MS320/ED28 /PS /U /4K
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Color	Pulse Start
Clear	8.31"	3.50"	20000	33000	4200	Cool White	Yes
Pack	Package Type	CRI	Burning Position	RoHS Compliant			
12	Box	65	Universal	Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

