



# S5845

MH1000/BT37/U/4K  
1000 watt; Metal Halide HID; Mogul base; BT37; Clear; 65 CRI;  
4200K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5845

| Item Number | UPC           | Watts         | Lamp Shape          | Base           | ANSI Base   | ANSI Code  | Lamp Code        |
|-------------|---------------|---------------|---------------------|----------------|-------------|------------|------------------|
| S5845       | 045923058455  | 1000          | BT37                | Mogul          | E39         | M47/E      | MH1000/BT37/U/4K |
| Finish      | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color      | Probe Start      |
| Clear       | 11.5"         | 4.63"         | 15000               | 110000         | 4200        | Cool White | Yes              |
| Pack        | Package Type  | CRI           | Burning Position    | RoHS Compliant |             |            |                  |
| 12          | Box           | 65            | Universal           | Yes            |             |            |                  |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S5845

MH1000/BT37/U/4K  
1000 watt; Metal Halide HID; Mogul base; BT37; Clear; 65 CRI;  
4200K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5845

| Item Number | UPC           | Watts         | Lamp Shape          | Base           | ANSI Base   | ANSI Code  | Lamp Code        |
|-------------|---------------|---------------|---------------------|----------------|-------------|------------|------------------|
| S5845       | 045923058455  | 1000          | BT37                | Mogul          | E39         | M47/E      | MH1000/BT37/U/4K |
| Finish      | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color      | Probe Start      |
| Clear       | 11.5"         | 4.63"         | 15000               | 110000         | 4200        | Cool White | Yes              |
| Pack        | Package Type  | CRI           | Burning Position    | RoHS Compliant |             |            |                  |
| 12          | Box           | 65            | Universal           | Yes            |             |            |                  |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

