



S5862

MP175/ED17/U
175 watt; Metal Halide HID; Medium base; ED17; Clear; 65
CRI; 4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Open Rated



S5862

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|---------------|-----------|----------------|---------------------|-------------|-----------|------------------|
| S5862 | 045923058622 | 175 | ED17 | Medium | E26 | M57/O | MP175/ED17/U |
| Finish | MOL In Inches | MOL in mm | Initial Lumens | Average Rated Hours | Kelvin Temp | CRI | Burning Position |
| Clear | 5.44" | 138.18 mm | 14000 | 12000 | 4000 | 65 | Universal |
| Open Rated | | | | | | Pack | |
| Yes | | | | | | 12 | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S5862

MP175/ED17/U
175 watt; Metal Halide HID; Medium base; ED17; Clear; 65
CRI; 4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Open Rated



S5862

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|---------------|-----------|----------------|---------------------|-------------|-----------|------------------|
| S5862 | 045923058622 | 175 | ED17 | Medium | E26 | M57/O | MP175/ED17/U |
| Finish | MOL In Inches | MOL in mm | Initial Lumens | Average Rated Hours | Kelvin Temp | CRI | Burning Position |
| Clear | 5.44" | 138.18 mm | 14000 | 12000 | 4000 | 65 | Universal |
| Open Rated | | | | | | Pack | |
| Yes | | | | | | 12 | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

