



# S7241

23R40/27  
23 watt; R40 Compact Fluorescent; 2700K; 82 CRI; Medium base; 120 volts

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7241

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S7241	045923072413	120	23	85W	R40	Medium	E26
Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
23R40/27	6.49"	5.00"	1090	10000	2700	Warm White	24/6
Package Type	CRI	CEC Status	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty	
Box	82	Lawful for sale in California	1.6 mg	Yes	Yes	<a href="#">2 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S7241

23R40/27  
23 watt; R40 Compact Fluorescent; 2700K; 82 CRI; Medium base; 120 volts

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7241

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S7241	045923072413	120	23	85W	R40	Medium	E26
Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
23R40/27	6.49"	5.00"	1090	10000	2700	Warm White	24/6
Package Type	CRI	CEC Status	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty	
Box	82	Lawful for sale in California	1.6 mg	Yes	Yes	<a href="#">2 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

