

S811+ Soft Starter with Digital Interface Module

S811+R10N3S



General Description

S811+ Soft Starter, 1000A, R-frame, Three-pole, 24V power, 200-600V operating voltage, 47-63 Hz, 1-2 conductors, #22-14 AWG wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display, -30°C to -50°C

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the product or eighteen (18) months from the date of shipment of the product, whichever occurs first.

Product Specifications

CE Marked

IEC 60947-4-2, EN 60947-4-2, UL Listed, UL Recognized, CSA file No. 3211-06, CSA Certified for Elevator Duty

Package: 10.000 x 13.000 x 9.500 in.

Package Weight: 12.500 lbs.

- Soft starter
- 1000A
- Modbus RTU
- R-frame
- 47-63 Hz
- 240 Vac
- 120 Vdc
- Three-pole
- -30°C to -50°C
- 200-600V
- NEMA 0
- Three-phase motors
- #22-14 AWG
- LCD
- Digital interface module
- NEMA Type 0
- 24V
- 1-2

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2014 Eaton
All Rights Reserved
Printed in USA
August 2014

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

EAT•N

Powering Business Worldwide