

Specifications

Photo is representative

Eaton S811+T30P3S

Eaton S811+ soft starter, Soft Starter 200MM
304 A Pump control with OPT Inside delta

General specifications

PRODUCT NAME	Eaton S811+ soft starter
CATALOG NUMBER	S811+T30P3S
UPC	786685559025
PRODUCT LENGTH/DEPTH	19 in
PRODUCT HEIGHT	12.5 in
PRODUCT WIDTH	14.5 in
PRODUCT WEIGHT	45 lb
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC 60947-4-2 EN 60947-4-2 UL Listed CSA Certified CSA Certified for Elevator Duty UL Recognized CSA file No. 3211-06



Product specifications

AMPERAGE RATING	95-304A
SPECIAL FEATURES	30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions
TYPE	Premium
FRAME SIZE	T
RATING	90 kW at 230 V, 160 kW at 380-400 V, 185 kW at 440 V

Resources

APPLICATION NOTES	S8x1 adjustment - Switching from S801+ to S811+
CATALOGS	Product Range Catalog Drives Engineering Soft Starter Product Family Overview
MULTIMEDIA	Soft Starter DS7 up to 32 A Soft starter DS7 up to 200 A
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S811+T30P3S
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton S811+T30P3S

Eaton S811+ soft starter, Soft Starter 200MM 304 A Pump control with OPT Inside delta

General specifications

PRODUCT NAME	Eaton S811+ soft starter
CATALOG NUMBER	S811+T30P3S
UPC	786685559025
PRODUCT LENGTH/DEPTH	19 in
PRODUCT HEIGHT	12.5 in
PRODUCT WIDTH	14.5 in
PRODUCT WEIGHT	45 lb
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC 60947-4-2 EN 60947-4-2 UL Listed CSA Certified CSA Certified for Elevator Duty UL Recognized CSA file No. 3211-06



Product specifications

AMPERAGE RATING	95-304A
SPECIAL FEATURES	30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions
TYPE	Premium
FRAME SIZE	T
RATING	90 kW at 230 V, 160 kW at 380-400 V, 185 kW at 440 V

Resources

APPLICATION NOTES	S8x1 adjustment - Switching from S801+ to S811+
CATALOGS	Product Range Catalog Drives Engineering Soft Starter Product Family Overview
MULTIMEDIA	Soft Starter DS7 up to 32 A Soft starter DS7 up to 200 A
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S811+T30P3S
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

