

# Eaton S811 V72N3S

Catalog Number: S811+V72N3S

Eaton S811+ soft starter, Soft Starter, 290MM, 720 A, with OPT Inside the Delta

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton S811+ soft starter	S811+V72N3S
UPC	Product Length/Depth
786685559162	23.5 in
Product Height	Product Width
11.5 in	16.5 in
Product Weight	Certifications
108 lb	Contact Manufacturer

**Amperage Rating**

850A

**Special features**

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

**Type**

Standard

**Frame size**

V

**Rating**

257 kW at 230 V, 475 kW at 380-400 V, 500 kW at 440 V

**Application notes**

S8x1 adjustment - Switching from S801+ to S811+

**Brochures**

S811+/S801+ soft starters

**Catalogs**

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - S811+V72N3S

Product Range Catalog Drives Engineering

**Drawings**

Type S811+ Soft Starter - V-frame

**Installation instructions**

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

**Multimedia**

Soft Starter DS7 up to 32 A

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

**Specifications and datasheets**

Eaton Specification Sheet - S811+V72N3S



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia