

Eaton S811 V72N3S

Catalog Number: S811+V72N3S

Eaton S811+ soft starter, Soft Starter, 290MM, 720 A, with OPT Inside the Delta



Photo is representative

General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+V72N3S
UPC	Product Length/Depth
786685559162	23.5 in
Product Height	Product Width
11.5 in	16.5 in
Product Weight	Certifications
108 lb	Contact Manufacturer

Amperage Rating

850A

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

Type

Standard

Frame size

V

Rating

257 kW at 230 V, 475 kW at 380-400 V, 500 kW at 440 V

Application notes

S8xL adjustment - Switching from S801+ to S811+

Brochures

S811+/S801+ soft starters

Catalogs

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - S811+V72N3S

Product Range Catalog Drives Engineering

Drawings

Type S811+ Soft Starter - V-frame

Installation instructions

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

Multimedia

Soft Starter DS7 up to 32 A

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+V72N3S