



S8132

F28T5/835/ENV
 28 watt; T5; Fluorescent; 3500K Neutral White; 85 CRI;
 Miniature Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8132

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8132	045923081323	28	T5	Miniature Bi Pin	G5	F28T5/835/ENV	0.63"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
45.8"	48"	2900	2700	24000	3500	Neutral White	40
Package Type	CRI	RoHS Compliant					
Sleeve	85	Yes					



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027





S8132

F28T5/835/ENV
 28 watt; T5; Fluorescent; 3500K Neutral White; 85 CRI;
 Miniature Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8132

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8132	045923081323	28	T5	Miniature Bi Pin	G5	F28T5/835/ENV	0.63"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
45.8"	48"	2900	2700	24000	3500	Neutral White	40
Package Type			CRI	RoHS Compliant			
Sleeve			85	Yes			



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

