



# S8668

FT40HL/841 /RS /ENV  
40 watt; pin-based Compact Fluorescent; 4100K; 82 CRI; 2G11 base

### Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8668

| Item Number    | UPC            | Watts               | Lamp Shape  | Base       | ANSI Base | Lamp Code           | Voltage |
|----------------|----------------|---------------------|-------------|------------|-----------|---------------------|---------|
| S8668          | 045923086687   | 40                  | T5          | 2G11       | 2G11      | FT40HL/841 /RS /ENV | 120     |
| MOL In Inches  | Initial Lumens | Average Rated Hours | Kelvin Temp | Color      | Pack      | Package Type        | CRI     |
| 22.5           | 3500           | 20000               | 4100        | Cool White | 10        | Box                 | 82      |
| RoHS Compliant |                |                     |             | UL Listed  |           |                     |         |
| Yes            |                |                     |             | Yes        |           |                     |         |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8668

FT40HL/841 /RS /ENV  
40 watt; pin-based Compact Fluorescent; 4100K; 82 CRI; 2G11 base

### Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8668

| Item Number    | UPC            | Watts               | Lamp Shape  | Base       | ANSI Base | Lamp Code           | Voltage |
|----------------|----------------|---------------------|-------------|------------|-----------|---------------------|---------|
| S8668          | 045923086687   | 40                  | T5          | 2G11       | 2G11      | FT40HL/841 /RS /ENV | 120     |
| MOL In Inches  | Initial Lumens | Average Rated Hours | Kelvin Temp | Color      | Pack      | Package Type        | CRI     |
| 22.5           | 3500           | 20000               | 4100        | Cool White | 10        | Box                 | 82      |
| RoHS Compliant |                |                     |             | UL Listed  |           |                     |         |
| Yes            |                |                     |             | Yes        |           |                     |         |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

