



S8952

4.5CTC/LED/3000K/E12/120V
 4.5 watt; B11 LED; 3000K; Candelabra base; 120 volts

Features

- Solid State LED lighting
- Decorative replacement lamp
- Long life
- Dimmable
- UL approved for totally enclosed fixtures

Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Leviton® 6674 Universal
- Leviton® IPLO6 Universal



S8952

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape | Base |
|----------------|---------------------------|-----------------------|-----------------|--|---------------|--------------------------------|---------------------|
| S8952 | 045923089527 | 120 | 4.5 | 40W | 0.93 | B11 | Candelabra |
| ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours |
| E12 | 4.5CTC/LED/3000K/E12/120V | Dimmable | Clear | 3 3/4" | 1 3/8" | 310 | 25000 |
| Kelvin Temp | Color | CRI | Beam Spread Deg | Operating Temperature | Pack | Package Type | ENERGY STAR |
| 3000 | Warm White | 80 | 290 | -20°C (-4°F) to a maximum of +45°C (113°F) | 12 | CD/1 | ENERGY STAR |
| RoHS Compliant | | UL or ETL Listed | | UL Classification | | Warranty | |
| Yes | | Yes | | Damp | | 3 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8952

4.5CTC/LED/3000K/E12/120V
 4.5 watt; B11 LED; 3000K; Candelabra base; 120 volts

Features

- Solid State LED lighting
- Decorative replacement lamp
- Long life
- Dimmable
- UL approved for totally enclosed fixtures

Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Leviton® 6674 Universal
- Leviton® IPLO6 Universal



S8952

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape | Base |
|----------------|---------------------------|-----------------------|-----------------|--|---------------|--------------------------------|---------------------|
| S8952 | 045923089527 | 120 | 4.5 | 40W | 0.93 | B11 | Candelabra |
| ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours |
| E12 | 4.5CTC/LED/3000K/E12/120V | Dimmable | Clear | 3 3/4" | 1 3/8" | 310 | 25000 |
| Kelvin Temp | Color | CRI | Beam Spread Deg | Operating Temperature | Pack | Package Type | ENERGY STAR |
| 3000 | Warm White | 80 | 290 | -20°C (-4°F) to a maximum of +45°C (113°F) | 12 | CD/1 | ENERGY STAR |
| RoHS Compliant | | UL or ETL Listed | | UL Classification | | Warranty | |
| Yes | | Yes | | Damp | | 3 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

