



# S9141

7R20/ E26/ 3000K/ Dimmable  
7 watt; LED R20; 3000K; 106° beam spread; Medium base; 120 volts; dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable

### Top 3 Compatible Dimmers

- Leviton® 6674 Universal
- Lutron® SELV300 ELV
- Cooper® TAL06-C1 TOGGLE LED



S9141

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9141	045923091414	7	R20	Medium	E26	7R20/ E26/ 3000K/ Dimmable	120

MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Incandescent Equivalent
3 15/16"	2.50"	540	25000	3000	Warm White	80	50W

Pack	Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed
24/6	Box	106	ENERGY STAR	Yes	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9141

7R20/ E26/ 3000K/ Dimmable  
7 watt; LED R20; 3000K; 106° beam spread; Medium base; 120 volts; dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable

### Top 3 Compatible Dimmers

- Leviton® 6674 Universal
- Lutron® SELV300 ELV
- Cooper® TAL06-C1 TOGGLE LED



S9141

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9141	045923091414	7	R20	Medium	E26	7R20/ E26/ 3000K/ Dimmable	120

  

MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Incandescent Equivalent
3 15/16"	2.50"	540	25000	3000	Warm White	80	50W

  

Pack	Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed
24/6	Box	106	ENERGY STAR	Yes	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

