





# S9454

15PAR38/LED/60'/5000K/120V/D  
 15 watt PAR38 LED; 5000K; 60' beam spread; Medium base;  
 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

### Compatible Dimmers

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASETEA PPD-6WCL-WH



S9454

| Item Number | UPC          | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base   | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9454       | 045923094545 | 120     | 15    | 90W                     | PAR38      | Medium | E26       |

| Lamp Code                    | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|------------------------------|-----------------------|--------|---------------|---------------|----------------|---------------------|-------------|
| 15PAR38/LED/60'/5000K/120V/D | Dimmable              | Silver | 5 3/16"       | 4 3/4"        | 1200           | 25000               | 5000        |

| Color         | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant | UL or ETL Listed |
|---------------|-----|-----------------|------|--------------|-------------|----------------|------------------|
| Natural Light | 80  | 60              | 12/6 | Box          | ENERGY STAR | Yes            | Yes              |

### Warranty

[3 Year Limited](#)



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027







# S9454

15PAR38/LED/60'/5000K/120V/D  
 15 watt PAR38 LED; 5000K; 60' beam spread; Medium base;  
 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

### Compatible Dimmers

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASETEA PPD-6WCL-WH



S9454

| Item Number | UPC          | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base   | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9454       | 045923094545 | 120     | 15    | 90W                     | PAR38      | Medium | E26       |

| Lamp Code                    | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|------------------------------|-----------------------|--------|---------------|---------------|----------------|---------------------|-------------|
| 15PAR38/LED/60'/5000K/120V/D | Dimmable              | Silver | 5 3/16"       | 4 3/4"        | 1200           | 25000               | 5000        |

| Color         | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant | UL or ETL Listed |
|---------------|-----|-----------------|------|--------------|-------------|----------------|------------------|
| Natural Light | 80  | 60              | 12/6 | Box          | ENERGY STAR | Yes            | Yes              |

### Warranty

[3 Year Limited](#)



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

