



# S9498

6.5MR16/LED/40'/40K/12V  
6.5 watt; LED MR16 LED; 4000K; 40' beam spread; GU5.3 base; 12 volts

### Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable

### Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9498

Item Number	UPC	Voltage	Watts	Lamp Shape	Base	ANSI Base	Lamp Code		
S9498	045923094989	12	6.5	MR16	GU5.3	GU5.3	6.5MR16/LED/40'/40K/12V		
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color		
Dimmable	Silver Back	1 3/4"	2"	540	25000	4000	Cool White		
CRI	Beam Spread Deg	Pack	ENERGY STAR	RoHS Compliant	UL or ETL Listed	Warranty			
80	40	12/48	ENERGY STAR Pending	Yes	Yes	<a href="#">3 Year Limited</a>			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9498

6.5MR16/LED/40'/40K/12V  
6.5 watt; LED MR16 LED; 4000K; 40' beam spread; GU5.3 base; 12 volts

### Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable

### Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9498

Item Number	UPC	Voltage	Watts	Lamp Shape	Base	ANSI Base	Lamp Code		
S9498	045923094989	12	6.5	MR16	GU5.3	GU5.3	6.5MR16/LED/40'/40K/12V		
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color		
Dimmable	Silver Back	1 3/4"	2"	540	25000	4000	Cool White		
CRI	Beam Spread Deg	Pack	ENERGY STAR	RoHS Compliant	UL or ETL Listed	Warranty			
80	40	12/48	ENERGY STAR Pending	Yes	Yes	<a href="#">3 Year Limited</a>			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

