



# S9593

9A19/LED/2700K/120V  
9 watt; A19 LED; Frosted; 2700K Medium base; 240° beam spread; 120 volts; Non-Dimmable

### Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable



S9593

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9593	045923095931	120	9	60W	A19	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
9A19/LED/2700K/120V	Non-Dimmable	Frosted	4 9/16"	2.38"	800	10000	2700

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	Warranty
Warm White	80	240	24/6	Box	Yes	Yes	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9593

9A19/LED/2700K/120V  
9 watt; A19 LED; Frosted; 2700K Medium base; 240° beam spread; 120 volts; Non-Dimmable

### Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable



S9593

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9593	045923095931	120	9	60W	A19	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
9A19/LED/2700K/120V	Non-Dimmable	Frosted	4 9/16"	2.38"	800	10000	2700

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	Warranty
Warm White	80	240	24/6	Box	Yes	Yes	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

