



S9595

9A19/LED/5000K/120V
9 watt; A19 LED; Frosted; 5000K Medium base; 240° beam spread; 120 volts; Non-Dimmable

Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable



S9595

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9595	045923095955	120	9	60W	A19	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
9A19/LED/5000K/120V	Non-Dimmable	Frosted	4 9/16"	2.38"	840	10000	5000

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	Warranty
Natural Light	80	240	24/6	Box	Yes	Yes	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9595

9A19/LED/5000K/120V
9 watt; A19 LED; Frosted; 5000K Medium base; 240' beam spread; 120 volts; Non-Dimmable

Features

- Solid State LED lighting
- A-Shaped replacement lamp
- Long life
- Non-Dimmable



S9595

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9595	045923095955	120	9	60W	A19	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
9A19/LED/5000K/120V	Non-Dimmable	Frosted	4 9/16"	2.38"	840	10000	5000

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	Warranty
Natural Light	80	240	24/6	Box	Yes	Yes	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

