



# S9633

6.5R20/LED/5000K/580L/120V  
6.5 watt; LED R20; 5000K; 107' beam spread; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9633

| Item Number         | Product Line                | UPC                        | Voltage                        | Watts           | Incandescent Equivalent | Power Factor  | Lamp Shape     |
|---------------------|-----------------------------|----------------------------|--------------------------------|-----------------|-------------------------|---------------|----------------|
| S9633               | DiTTO                       | 045923096334               | 120                            | 6.5             | 50W                     | 0.90          | R20            |
| Base                | ANSI Base                   | Lamp Code                  | Dimmable/Non-Dimmable          | Finish          | MOL In Inches           | MOD In Inches | Initial Lumens |
| Medium              | E26                         | 6.5R20/LED/5000K/580L/120V | Dimmable                       | Frosted         | 3 15/16"                | 2.50"         | 580            |
| Average Rated Hours | Kelvin Temp                 | Color                      | CRI                            | Beam Spread Deg | Pack                    | Package Type  | RoHS Compliant |
| 25000               | 5000                        | Natural Light              | 80                             | 107             | 24/6                    | Box           | Yes            |
| UL or ETL Listed    | UL Classification           |                            | Warranty                       |                 |                         |               |                |
| Yes                 | cULus - Damp Location Rated |                            | <a href="#">3 Year Limited</a> |                 |                         |               |                |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9633

6.5R20/LED/5000K/580L/120V  
6.5 watt; LED R20; 5000K; 107' beam spread; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9633

| Item Number         | Product Line                | UPC                        | Voltage                        | Watts           | Incandescent Equivalent | Power Factor  | Lamp Shape     |
|---------------------|-----------------------------|----------------------------|--------------------------------|-----------------|-------------------------|---------------|----------------|
| S9633               | DiTTO                       | 045923096334               | 120                            | 6.5             | 50W                     | 0.90          | R20            |
| Base                | ANSI Base                   | Lamp Code                  | Dimmable/Non-Dimmable          | Finish          | MOL In Inches           | MOD In Inches | Initial Lumens |
| Medium              | E26                         | 6.5R20/LED/5000K/580L/120V | Dimmable                       | Frosted         | 3 15/16"                | 2.50"         | 580            |
| Average Rated Hours | Kelvin Temp                 | Color                      | CRI                            | Beam Spread Deg | Pack                    | Package Type  | RoHS Compliant |
| 25000               | 5000                        | Natural Light              | 80                             | 107             | 24/6                    | Box           | Yes            |
| UL or ETL Listed    | UL Classification           |                            | Warranty                       |                 |                         |               |                |
| Yes                 | cULus - Damp Location Rated |                            | <a href="#">3 Year Limited</a> |                 |                         |               |                |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

