



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S9639 16.5W Led BR40 30K 103' BM

Satco

Catalog Number	S9639
Manufacturer	Satco
Description	Led Lamp, 103 ° Beam Angle, 3000 K, 1200 LM Brightness (Lumens), 16.5 W, 120 V, Frosted, 25000 H Average Life, E26 Medium Base, Dimmable, 5 In Diameter, 6-7/16 In Height, 0.91 Power Factor, -13 °F Operating Temperature, +113 °F Operating Temperature, 85 W, 5 Yr Warranty, 0.66 LB
Weight per unit	0.8200 (lbs/each)
Product Category	Led Lamps & Modules

### Features

Base	E26
brightness	460
lumens	1200

### Material, Color, and Finish

Color	White
color rendering index (cri)	80

### Dimensions and Weight

Size	6.44
------	------

### Descriptions

Description	16.5W LED BR40 30K 103' BM
extra long description	SATCO S9639 16.5BR40/LED/3000K/1230

### Manufacturer Information

GTIN	00045923096396
UPC	045923096396

### Taxonomies, Classifications, and Categories

Category Description	LED REFLECTOR GU, MR R SHAPE LAMPS
Type	BR LED

### Packaging

Carton	1
Weight Per each	0.82

### Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
-----------------------	--