



# S9751

40W/LED/HID/MB/5000K/100-277V  
 40 watt - LED HID Replacement; 5000K; Mogul extended base;  
 100-277 volts

## Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay or low bay
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- 5 year limited warranty



S9751

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)

Available June 2016

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9751	Hi-Pro	045923097515	100 - 277	40	300W	65W	175W

Power Factor	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
0.90	Mogul Extended	EX39	40W/LED/HID/MB/5000K/100-277V	Non-Dimmable	White	7 7/8"	3 13/16"

Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type
5200	50000	5000	Natural Light	80+	Adjustable: 360; 270; 180	16	Box

RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty
Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	<a href="#">5 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9751

40W/LED/HID/MB/5000K/100-277V  
 40 watt - LED HID Replacement; 5000K; Mogul extended base;  
 100-277 volts

## Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay or low bay
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- 5 year limited warranty



S9751

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)

Available June 2016

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9751	Hi-Pro	045923097515	100 - 277	40	300W	65W	175W

Power Factor	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
0.90	Mogul Extended	EX39	40W/LED/HID/MB/5000K/100-277V	Non-Dimmable	White	7 7/8"	3 13/16"

Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type
5200	50000	5000	Natural Light	80+	Adjustable: 360; 270; 180	16	Box

RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty
Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	<a href="#">5 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

