

# S9879 A19 LED

## 8.5A19/CL/LED/E26/27K/90CRI

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	8.5
Color Temperature	2700
Color Rendering Index CRI	91



### Lighting Facts Per Bulb

<b>Brightness</b>	<b>800 lumens</b>
<b>Estimated Energy Cost</b>	<b>\$0.96</b>
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
<b>Average Life</b>	<b>13.7 years</b>
Based on 3 hrs/day	
<b>Light Appearance</b>	
<b>Energy Used</b>	<b>8 watts</b>

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9879	LED	*20045923098790	120	8.5	n/a	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	8.5A19/CL/LED/E26/27K/90CRI	Yes	n/a	4	2 3/8	800	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	91	360	24	Box	Yes	Yes

# S9879 A19 LED

## 8.5A19/CL/LED/E26/27K/90CRI

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	8.5
Color Temperature	2700
Color Rendering Index CRI	91



### Lighting Facts Per Bulb

Brightness	800 lumens
Estimated Energy Cost	\$0.96
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	13.7 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	8 watts

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9879	LED	*20045923098790	120	8.5	n/a	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	8.5A19/CL/LED/E26/27K/90CRI	Yes	n/a	4	2 3/8	800	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	91	360	24	Box	Yes	Yes