

## LED T8 LAMPS

# 14W Linear LED ballast by-pass T8 series

## Double ended wiring

### Applications/ Features

- Works with existing sockets—shunted or non-shunted
- Reduces labor costs for installation
- Built-in shock resistant circuit (not hot until both ends are installed)
- No ballast or external driver required
- Direct wire 120-277V line voltage
- All glass tube
- Long life—50,000 hours
- Damp location
- c-UL-us classified
- DLC listed\*
- 5 Year warranty



### LED Fluorescent Replacement Lamps

Item Number	Lamp Description	W	CRI	Base Type	Bm	CCT	Lm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9913*	14T8/LED/48-830/BP	14	82	Med Bi-Pin	210°	3000K	1800	48	50K	045923099137	10
S9914*	14T8/LED/48-835/BP	14	82	Med Bi-Pin	210°	3500K	1800	48	50K	045923099144	10
S9915*	14T8/LED/48-840/BP	14	82	Med Bi-Pin	210°	4000K	1800	48	50K	045923099151	10
S9916*	14T8/LED/48-850/BP	14	82	Med Bi-Pin	210°	5000K	1800	48	50K	045923099168	10

# Satco 33W, 8' LED T8 lamps

Direct replacement for linear fluorescent T8 lamps in existing fixtures with electronic instant start ballasts. No rewiring required\*\*

### Applications/ Features

- Over 40% energy savings vs standard 8' T8 systems
- All glass tube
- Direct replacement solution allows the fixture to maintain the Original UL and CSA Compliance
- Long life—50,000 hours
- Instant on to full brightness/no flickering
- Damp location
- NSF certified\*
- 5 Year warranty



### LED Fluorescent Replacement Lamps

Item Number	Lamp Description	W	CRI	Base Type	Bm	CCT	Lm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9700*	33T8/LED/96-840/DR	33	82	Single Pin	230°	4000K	4400	96	50K	045923097003	10
S9701*	33T8/LED/96-850/DR	33	82	Single Pin	230°	5000K	4400	96	50K	045923097010	10

\*\*May not be compatible with all instant start ballasts. Visit [www.satco.com](http://www.satco.com) for an approved list.