



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SBC2C Split Bolt Connector *Panduit Corporation*

Catalog Number	SBC2C
Manufacturer	Panduit Corporation
Description	Split Bolt Connector, #6 Awg (Stranded) Conductor Size, #2 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 1.23 In Overall Length
Weight per unit	11.7 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
media	Yes
Voltage Rating	600 V

Material, Color, and Finish

Finish	blank
--------	-------

Descriptions

Also Known As...	Monkey balls Split Bolt Connector Kearnys Bug
Description	SPLIT BOLT CONNECTOR
extra long description	PAN SBC2-C Pan-Lug™ SBC2-C Mech Con
similar brands	Servit®

Manufacturer Information

Brand	PANDUIT
GTIN	00074983627233
UPC	074983627233

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Mechanical Split Bolt Connector

Packaging

Carton	100
Weight Per each	11.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

UL listed to 467 and 486 and CSA certified for use up to 600V &
Temperature Rated to 90°C
