



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SBC3C Split Bolt Conn *Panduit Corporation*

Catalog Number	SBC3C
Manufacturer	Panduit Corporation
Description	Split Bolt Connector, #8 Awg (Stranded) Conductor Size, #4 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 1.16 In Overall Length, 1 LB/Ea
Weight per unit	1.0 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
media	Yes
Voltage Rating	600 V

Material, Color, and Finish

Finish	Uncoated
--------	----------

Descriptions

Also Known As...	Monkey balls Bug Kearnys Split Bolt Connector
Description	SPLIT BOLT CONN
extra long description	PAN SBC3-C Pan-Lug™ SBC3-C Mech Con
similar brands	Servit®

Manufacturer Information

Brand	PANDUIT
GTIN	00074983627226
UPC	074983627226

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Mechanical Split Bolt Connector

Packaging

Carton	1
Package	100
Weight Per each	1

Uses, Certifications, and Standards

standard	UL listed to 467 and 486 and CSA certified for use up to 600V & Temperature Rated to 90°C
----------	---