



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SC8 #8 Cu Butt Splice *Nsi Industries*

| | |
|------------------|---|
| Catalog Number | SC8 |
| Manufacturer | Nsi Industries |
| Description | Standardbarrel TINNEDCOPPERSPLICE8 Awg Standard Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed. |
| Weight per unit | 0.0140 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|--------|
| Material | Copper |
| Number of Conductors | 2 |
| Poles | 600 V |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Red |
| Finish | Tin Plated |

Dimensions and Weight

| | |
|------|----------------------------|
| Size | L=.900 - OD=.270 - ID=.170 |
|------|----------------------------|

Descriptions

| | |
|------------------------|---|
| Description | #8 CU BUTT SPLICE |
| extra long description | NSI SC-8 8 AWG Copper Short Barrel |
| Features | Standard Barrel Tinned Copper Splice for 8 AWG: Standard Barrel Tinned Copper Splices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Long Description | StandardBarrel TinnedCopperSplice8 AWG Standard Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Product Type | 8 Awg Copper Short Barrel Splice - Red |
| Special Features | # 8 AWG (STR) - CU Splice |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381037008 |
| Manufacturers Part Number | SC-8 |
| UPC | 662381037008 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Short Barrel - CU Splice |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.014 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| standard | UL486A/B, UL467 (8 AWG -3/0 AWG) |
| Temperature Rating | 90 C |