



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SCS8L #8AWG Cu CMP Butt Splice

Panduit Corporation

|                  |   |
|------------------|---|
| Catalog Number   | SCS8L   |
| Manufacturer     | Panduit Corporation                               |
| Description      | Copper Butt Splice, Standard Barrel, #8 Awg Wire. |
| Weight per unit  | 0.9000 (lbs/each)                                 |
| Product Category | Large Terminals & Connectors                      |

### Features

|                |        |
|----------------|--------|
| Material       | Copper |
| media          | Yes    |
| Voltage Rating | NA     |

### Material, Color, and Finish

|        |            |
|--------|------------|
| Color  | Red        |
| Finish | Tin-Plated |

### Dimensions and Weight

|      |    |
|------|----|
| Size | NA |
|------|----|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | #8AWG CU CMP BUTT SPLICE                              |
| extra long description | PAN SCS8-L Pan-Lug™ SCS8-L Comp. Sp                   |
| Long Description       | Copper butt splice, standard barrel, #8 AWG wire.     |
| Product Type           | Pan-Lug™ SCS8-L Comp. Splice, Tin-Plated Copper, PK50 |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | PANDUIT        |
| GTIN                      | 00074983903009 |
| Manufacturers Part Number | SCS8-L         |
| UPC                       | 074983903009   |

### Taxonomies, Classifications, and Categories

|      |                    |
|------|--------------------|
| Type | Compression Splice |
|------|--------------------|

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 50  |
| Weight Per each | 0.9 |

### Uses, Certifications, and Standards

|          |     |
|----------|-----|
| standard | Yes |
|----------|-----|