



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **SDL615930D 120V, 60HZ, 15W, 0.125, CRI90, 30K, 992 White**

*Topaz - Southwire CO LLC*

Catalog Number	SDL615930D
Manufacturer	Topaz - Southwire CO LLC
Description	Led Ceiling Mount Light Fixture, White Finish; 7.4 Inch; 15.5 Watt Wattage; Led Lamp Type; Rohs Compliant; Mounting Type Surface; Nominal Size 6 Inch; Voltage Rating 120 Volt; Beam Angle 35 Degree; Intensity 1050 Lumen; Color Rendering Index 90
Weight per unit	0.9000 (lbs/each)
Product Category	Led Surface Architectural & SP

### **Features**

Lamp Type	LED
Wattage	15.5 Watt

### **Material, Color, and Finish**

Finish	white
--------	-------

### **Dimensions and Weight**

Width	7.4 Inch
-------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information

RoHS Compliant; Mounting Type Surface; Nominal Size 6 Inch; Voltage Rating 120 Volt; Beam Angle 35 Degree; Intensity 1050 Lumen; Color Rendering Index 90; Color Temperature Rating 3000 Kelvin; Efficacy Rating 65 Lumen per Watt; Lamp Life 50000 Hour; Tempe

Commodity Description

LED SURFACE ARCHITECTURAL & SPECIFICATION LIGHTING

Description

120V,60HZ,15W,0.125,CRI90,30K,992 WHITE

extra long description

WHITE FINISH; 7.4 INCH; 15.5 WATT WATTAGE; LED LAMP TYPE; ROHS COMPLIANT; MOUNTING TYPE SURFACE; NOMINAL SIZE 6 INCH; VOLTAGE RATING 120 VOLT; BEAM ANGLE 35 DEGREE; INTENSITY 1050 LUMEN; COLOR RENDERING INDEX 90; COLOR TEMPERATURE RATING 3000 KELVIN; EFFICACY RATING 65 LUMEN PER WATT; LAMP LIFE 50000 HOUR; TEMPERATURE RATING -4 TO 104 DEG F; APPLICATION RESIDENTIAL, COMMERCIAL, DAMP AND WET LOCATION; APPROVAL UL; APPLICABLE STANDARD NEC 410.16 (A)(3)/(C)(5), TITLE 24, NFPA

Features

Topaz's 6 , 15 watt, 3000K, LED Surface Mount Disk Light with white finish are easy-to-install for new construction as well as retrofit applications and are designed to be mounted to most standard 4" J-boxes. Perfect for residential or commercial applications including bathrooms, closets, storage areas, hallways and living areas, they offer exceptional color rendering of 90 CRI and are dimmable down to 5% with standard incandescent or LED style leading edge dimmers. Their optical design provides a wide bea

Long Description

LED CEILING MOUNT LIGHT FIXTURE, WHITE FINISH; 7.4 INCH; 15.5 WATT WATTAGE; LED LAMP TYPE; ROHS COMPLIANT; MOUNTING TYPE SURFACE; NOMINAL SIZE 6 INCH; VOLTAGE RATING 120 VOLT; BEAM ANGLE 35 DEGREE; INTENSITY 1050 LUMEN; COLOR RENDERING INDEX 90

Product Type

Led Ceiling Mount Light Fixture

## Manufacturer Information

Brand

TOPAZ

GTIN

00751338002753

Manufacturers Part Number

SDL6/15/930/D-28

UPC

751338002753

## Taxonomies, Classifications, and Categories

Category Description

Fuses & Fuse Accessories

## Availability

Status

Inactive



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.9