ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

SE00W144PCS 14/4 SEOOW 600V BLACK CORD PCS

SOUTHWIRE COMPANY

Catalog Number	SE00W144PCS
Manufacturer	SOUTHWIRE COMPANY
Description	Portable Cord, Stranded, 41/30 mm Core Strands, #14 AWG Conductor Size, Copper Conductor Material, Thermoplastic Elastomer (TPE) Jacket Material, Thermoplastic Elastomer (TPE) Insulation Material, 15 A, Black, Green, Red, White, 4 Conductors, 250 ft Overall Length, 0.575 in Outside Diameter, 0.045 in Insulation Thickness, -50 °C Operating Temperature, +105 °C Operating Temperature, 0.18 lb
Weight per unit	0.1900 (lbs/ft)
Product Category	Seow-Seoow

Features

Conductor Size	14 AWG
Number Of Conductors	4
Stranding	41/30 STRANDS
Voltage Rating	600 V

Material, Color, and Finish

Color Code	BLACK, WHITE, RED, GREEN
Conductor Material	Bare Copper
Insulation Material	T-Prene Thermoplastic Elastomer
Jacket Color	BLACK
Jacket Material	Chemical/Oil/Water Resistant Seoprene Thermoplastic Elastomer

Dimensions and Weight

Length	250 ft
Outer Diameter	0.565 INCH

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Descriptions

Additional Information	ROHS Compatible; Applicable Standard NEC 400, Federal Specification JC-580B; Current Rating 15 Ampere; Insulation Thickness 0.045 Inch
Commodity Description	SEOW - SEOOW - 600V CORD & CABLE
Description	14/4 SEOOW 600V BLACK CORD PCS
Long Description	14/4 SEOOW SEOPRENE 250R PORTABLE CORD, SEOOW TYPE; 250 FT; 0.565 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 62, CSA C22.2, MSHA APPROVAL
Extra Long Description	SEOOW TYPE; 250 FT; 0.565 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 62, CSA C22.2, MSHA APPROVAL; INDUSTRIAL CONTROL, MOTOR CONTROL, MINING, PORTABLE POWER DISTRIBUTION, PUSHBUTTON REMOTE CONTROL, ROBOTIC SYSTEM, STAGE EQUIPMENT, LIGHTING APPLICATION; 600 V VOLTAGE RATING; -50 TO 105 DEG C TEMPERATURE RATING; 4 CONDUCTOR(S); T-PRENE THERMOPLASTIC ELASTOMER INSULATION MATERIAL; 14 AWG CONDUCTOR SIZE; BLACK, WHITE, RED, GREEN COLOR CODE; CHEMICAL/OIL/WATER RESISTANT SEOPRENE THERMOPLASTIC ELAST

Manufacturer Information

Brand	Cables & Cords Southwire Seoprene[R]
Manufacturers Part Number	224270408
Model	224
UPC	885800

Taxonomies, Classifications, and Categories

Category Description	Portable Cords, Voice, Data, Video Wire & Cable
Type	SEOOW

Packaging

Carton	1
Weight Per Each	0.1900 (lbs/ft)

Uses, Certifications, and Standards

Application	Industrial Control, Motor Control, Mining, Portable Power Distribution, Pushbutton Remote Control, Robotic System, Stage Equipment, Lighting
Approval	UL 62, CSA C22.2, MSHA
Temperature Rating	-50 TO 105 DEG C