



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

SE25PSCTR0 1/4" BLK Expn Sleeve, 200' Roll *Panduit Corporation*

Catalog Number	SE25PSCTR0
Manufacturer	Panduit Corporation
Description	Fray Resistant Braided Expandable Sleeving, .25" (6.4 MM) Diameter, Can Be Cut With A Pair Of Scissors and Provides Continuous Abrasion Resistance For Wires, Cables, and Tubing. The Lightweight, Durable Protection Is Flexible and The Open Weave Will Not Trap Heat or Humidity. Polyethylene Terephthalate. 200 FT (61.0 M) Reel. Color Black.
Weight per unit	1.1 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Material	PET
media	Yes
Nominal Size	0.25

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Diameter	0.16 - 0.44
Length	200

Descriptions

Description	1/4" BLK EXPN SLEEVE, 200' ROLL
extra long description	PAN SE25PSC-TR0 Pan-Wrap™ SE25PSC-T
Long Description	Fray resistant braided expandable sleeving, .25" (6.4 mm) diameter, can be cut with a pair of scissors and provides continuous abrasion resistance for wires, cables, and tubing. The lightweight, durable protection is flexible and the open weave will not trap heat or humidity. Polyethylene Terephthalate. 200 ft (61.0 m) reel. Color Black.
Product Type	Pan-Wrap™ SE25PSC-TR0 Fray Resistant Sleeving, Black, Pet, 0

Manufacturer Information

Brand	PANDUIT
GTIN	00074983816460
Manufacturers Part Number	SE25PSC-TR0
UPC	074983816460

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Braided Expandable Sleeving



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per roll	1.13

Uses, Certifications, and Standards

Application	(1) Provides Continuous Abrasion Protection for Wires, Cables, Hoses, and Tubing; (2) Highly Flexible Open Weave will not Trap Heat or Humidity; (3) Allows for Use with Irregular Shapes
standard	CSA Certified, Compliant with U.S. and European passenger rail standards, UL Recognized E116868; RoHS Compliant
Temperature Rating	257