



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SG3A0030KB D16 SNTL-G 3PH 30KVA 480D-208Y/120V AI 60HZ 150C 3 *Hammond Power Solutions*

Catalog Number	SG3A0030KB
Manufacturer	Hammond Power Solutions
Description	600V Class Three Phase DOE2016 and Nrcan 2019 Compliant Energy Efficient Distribution Transformer, 480D PV, 208Y/120 SV, 30 Kva, 3PH, Aluminum Wound
Weight per unit	310.0 (lbs/each)
Product Category	Three Phase Energy Efficient D

### Features

kva rating	30
Number of Phases	3
Number of Taps	ST-20 compliant
Phase	3PH Delta-Wye-N
Primary Voltage	480D
Secondary Voltage	208Y/120

### Dimensions and Weight

Height	28.8
Length	23.8
Width	25.8

### Descriptions

Description	D16 SNTL-G 3PH 30KVA 480D-208Y/120V AL 60HZ 150C 3
extra long description	3PH 30KVA 480D-208Y/120V AL 150C
Features	Optional infrared windows available
Long Description	600V Class Three Phase DOE2016 and NRCAN 2019 Compliant Energy Efficient Distribution Transformer, 480D PV, 208Y/120 SV, 30 kVA, 3PH, Aluminum Wound
Product Type	D16 SNTL-G 3PH 30KVA 480D-208Y/120V AI 60HZ 150C 3R
Short Description	3PH 30kVA 480D-208Y/120V 150C
Special Features	Meets current DOE 10 CFR part 431 (2016) and C802.2 efficiencies in an outdoor type enclosure. Smaller kVA sizes have standard input and/or output lugs, knockouts, and wall mounting brackets to save installation costs.

### Manufacturer Information

Brand	HPS
GTIN	00803423121952
Manufacturers Part Number	SG3A0030KB
UPC	803423121952



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	3 PHASE TRANSFORMERS
Type	Transformer > Distribution > DOE 2016 Energy Efficient > General Purpose > Three Phase

## Packaging

Carton	1
Weight Per each	310

## Uses, Certifications, and Standards

Application	General purpose for supplying appliance, lighting, motorized machine and power loads from electrical distribution systems.
Enclosure	DH2-N3R - Indoor or Outdoor
Frequency Rating	60
Mounting standard	Floor or Wall/Ceiling Mount CSA, UL
Temperature Rating	Typical 30 Average/ 40 Maximum