



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SGB38840 3" Diecast Split Ground Bushing

Bridgeport Fittings

Catalog Number	SGB38840
Manufacturer	Bridgeport Fittings
Description	Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 3 Inch, 6-250 Lug
Weight per unit	0.5610 (lbs/each)
Product Category	Aluminum

Features

Material	Zinc Alloy
media	Yes

Material, Color, and Finish

Color	Grey with Black Insulator
Finish	Ball burnish

Dimensions and Weight

Size	3
------	---

Descriptions

Description	3" DIECAST SPLIT GROUND BUSHING
extra long description	BPT SGB-38840 3" SPLT GND BSH #6-25
Features	Split Bushings install after the wire pull. No more burning through bushings or fighting with pullers. Save time and effort too!
Long Description	Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 3 Inch, 6-250 Lug
Product Type	3" SPLT GND BSH #6-250MCM
Special Features	Grounding Lug Wire Capacity # 6 - #250

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747938855
Manufacturers Part Number	SGB38840
UPC	781747938855

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	SPLIT

Trade Size

Trade Size	3
------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 25

Weight Per each 0.561

Uses, Certifications, and Standards

Application Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations!

standard cULus

Temperature Rating 150°C