

Bridgeport Fittings Inc.


705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

Grounding - Zinc

Images





Dimension A in Inches: 2.49
Dimension B in Inches: 4.08
Dimension C in Inches: 0.73
Dimension D in Inches: 2.87
Dimension E in Inches: 4.00

Application

Used in situations where wires have already been pulled through conduit or EMT fittings, and an insulated Grounding bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed to UL514B and UL467 specifications. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations!

Product Information

Material: Zinc Alloy

Finish:

Ball Burnished, Mirror Smooth,
Grounding lug: Tin Electro-plate

Certifications & Codes:

Federal Specification A-A-50553

Number:

NEMA Standard:

UL File Number:

E20412

UL Standard: UL514B,UL467 UNSPSC: 39121312

Patent Number: 7,182,611; 6,840,782;

8,419,449

Catalog ID: SGB-38840

UPC Number: 78174793885

Description: Split Bushing, Insulated, Grounding, Zinc Die

Cast, Size 3 Inch, 6-250 Lug

Application: Used in situations where wires have already been pulled through conduit or EMT fittings, and an insulated Grounding bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed to UL514B and UL467 specifications. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations!

Trade Size: 3"

Std Pkg Qty: 25