

Specifications

Eaton SGS50

Eaton standard support grip, Closed Mesh Single Eye, 7" bale, 770 lbs break, 0.50-0.62" cord diameter, 11" mesh length, Tin-Coated Bronze

Product specifications

| | |
|-------------------------|------------------------|
| SPECIAL FEATURES | Closed Mesh Single Eye |
| TYPE | Standard support grip |
| CORD DIAMETER | 0.50-0.62 in |
| MATERIAL | Tin-Coated Bronze |
| BALE LENGTH | 7 in |
| BREAK STRENGTH | 770 lbs |
| MESH LENGTH | 11 in |

General specifications

| | |
|-----------------------------|-----------------------------|
| PRODUCT NAME | Eaton standard support grip |
| CATALOG NUMBER | SGS50 |
| UPC | 040893647081 |
| PRODUCT LENGTH/DEPTH | 0.581 in |
| PRODUCT HEIGHT | 19.2 in |
| PRODUCT WIDTH | 1.729 in |
| PRODUCT WEIGHT | 0.075 lb |
| CERTIFICATIONS | CSA Certified |



Powering Business Worldwide