



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SH104 1-1/4" 5H Al Svce Cap

*Abb Installation Products, Inc*

|                  |   |
|------------------|---|
| Catalog Number   | SH104   |
| Manufacturer     | Abb Installation Products, Inc  |
| Description      | Cap, Clamp-Type Service, Conduit Size 1-1/4 Inch, Number Of Holes 5, Size 2(19/32 Inch) 3(5/8 Inch), Aluminum, For Rigid/Intermediate or Thinwall, Pack Of 10 |
| Weight per unit  | 0.3750 (lbs/each)   |
| Product Category | Service Entrance CBL Fittings   |

### Features

|          |          |
|----------|----------|
| Material | Aluminum |
|----------|----------|

### Dimensions and Weight

|      |       |
|------|-------|
| Size | 1-1/4 |
|------|-------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1-1/4" 5H AL SVCE CAP   |
| extra long description | ABB SH 104 1 1/4 SVCE CAP,CLMP,RGD  |
| Long Description       | Cap, Clamp-Type Service, Conduit Size 1-1/4 Inch, Number of Holes 5, Size 2(19/32 Inch) 3(5/8 Inch), Aluminum, For Rigid/Intermediate or Thinwall, Pack of 10 |
| Product Type           | 1 1/4 Svce Cap, CLMP, RGD/Imc/Emt, Al   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Steel City     |
| GTIN                      | 00785991433562 |
| Manufacturers Part Number | SH 104         |
| UPC                       | 785991433562   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods |
| Type                 | Cable Caps   |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 10    |
| Weight Per each | 0.375 |

### Uses, Certifications, and Standards

|          |           |
|----------|-----------|
| standard | UL E13938 |
|----------|-----------|