



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SHC1040CR Cordcon, STR ML, .50-.63", 1", Nyl, Gy *Hubbell Wiring Devices*

Catalog Number	SHC1040CR
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Cord Connectors, Straight Male, .50-.63", 1", Nylon
Weight per unit	0.1500 (lbs/each)
Product Category	Cable & Cord Grips

Features

Material	Nylon
Number of Conductors	Single
pallet quantity	4725

Material, Color, and Finish

Color	Gray
Color Code	BROWN

Dimensions and Weight

Size	1.88 in x 1.88 in x 2.45 in
------	-----------------------------

Descriptions

Description	CORDCON, STR ML, .50-.63", 1", NYL, GY
extra long description	HWDC SHC1040CR CORDCON, STR ML, .50
Features	Cord Connectors - Hubbell has the broadest line and the widest choice of materials in the industry. NPT hub sizes from 1/4" to 3" in straight male end, 90°, 45°, female and underground feed connectors. They are available in your choice of aluminum, plated steel, nylon and stainless steel. The zinc-plated steel cord connectors offers the strength of steel and the corrosion resistance of zinc-plating. These heavy-duty connectors hold up to most manufacturing chemicals including acid solutions, solvents and oth
Long Description	Kellems Wire Management, Cord Connectors, Straight Male, .50-.63", 1", Nylon
Product Type	Cordcon, STR ML, .50-.63", 1", Nyl, Gy
Special Features	Standard Product

Manufacturer Information

Brand	Hubbell Wiring Devices
GTIN	00783585208121
Manufacturers Part Number	SHC1040CR
series	Standard Duty
UPC	783585208121



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type STRAIGHT MALE

Packaging

Carton 1

Package 15

Weight Per each 0.15

Uses, Certifications, and Standards

Application Straight Male- Form 4

environmental conditions Suitable for use in wet locations when used with a listed nylon washer between box and fitting.

Mounting Locknut or Tapped Opening

nema rating 12;4;4X;NEMA Type 4, 4X, 12 and 13

standard UL Listed

Temperature Rating Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)