



Product Description

MECHANIX ORANGE is formulated w/ the natural power of citrus. Quickly cleans away the toughest soils. Used with pH balanced to be gentle on hands. It's serious scrubbing power comes from fine grade pumice, leaves hands fresh.

Product Specifications

| | |
|--------------------------|-------------------------------------|
| Applications | Hands/skin, industrial sites. |
| Unit Package | 16 Ounce Squeeze Bottle |
| Description | |
| Generic Description 1 | Citrus Lotion Hand Cleaner w/Pumice |
| Brand | Sta-Lube |
| Net Fill | 16 Fl Oz |
| UPC Code | 0 72213 01712 0 |
| Unit Dimensions- Inches | 8.25H x 2W x 3.5D |
| Units Per Case | 12 |
| Case Dimensions- Inches | 8.75H x 7.5W x 11D |
| Cases Per Pallet | 120 |
| Lbs. Per Case | 15 |
| 1 2 of 5 Code | 30072213171205 |
| Appearance | Thick White Lotion w/Pumice |
| Odor | Natural Citrus |
| Flashpoint - TCC Method | >210°F |
| Specific Gravity | 0.95 to 1.1 |
| pH | 6.2 to 7.2 |
| Flammability | Non-flammable |
| Plastic Safe | Yes |
| Evaporation Rate | <1 (butyl acetate=1) |
| Propellant | None |
| NSF Registered | No |
| DOT Proper Shipping Name | Not Regulated |
| VOC % (Federal) | 6.2 |
| VOC g/L (Federal) | 60.76 |
| VOC Lbs./Gal. (Federal) | 0.51 |
| Compliant For CA | Yes |
| VOC Category | Heavy Duty Hand Cleaners |
| CA VOC Limit | 8% |
| OTC VOC Limit | 8% |



Product Description

MECHANIX ORANGE is formulated w/ the natural power of citrus. Quickly cleans away the toughest soils. Used with pH balanced to be gentle on hands. It's serious scrubbing power comes from fine grade pumice, leaves hands fresh.

Product Specifications

| | |
|--------------------------|-------------------------------------|
| Applications | Hands/skin, industrial sites. |
| Unit Package | 16 Ounce Squeeze Bottle |
| Description | |
| Generic Description 1 | Citrus Lotion Hand Cleaner w/Pumice |
| Brand | Sta-Lube |
| Net Fill | 16 Fl Oz |
| UPC Code | 0 72213 01712 0 |
| Unit Dimensions- Inches | 8.25H x 2W x 3.5D |
| Units Per Case | 12 |
| Case Dimensions- Inches | 8.75H x 7.5W x 11D |
| Cases Per Pallet | 120 |
| Lbs. Per Case | 15 |
| I 2 of 5 Code | 30072213171205 |
| Appearance | Thick White Lotion w/Pumice |
| Odor | Natural Citrus |
| Flashpoint - TCC Method | >210°F |
| Specific Gravity | 0.95 to 1.1 |
| pH | 6.2 to 7.2 |
| Flammability | Non-flammable |
| Plastic Safe | Yes |
| Evaporation Rate | <1 (butyl acetate=1) |
| Propellant | None |
| NSF Registered | No |
| DOT Proper Shipping Name | Not Regulated |
| VOC % (Federal) | 6.2 |
| VOC g/L (Federal) | 60.76 |
| VOC Lbs./Gal. (Federal) | 0.51 |
| Compliant For CA | Yes |
| VOC Category | Heavy Duty Hand Cleaners |
| CA VOC Limit | 8% |
| OTC VOC Limit | 8% |