

**SL35911 -- Nickel Anti-Seize Lubricating Compound, 8 Wt Oz**



**Product Description**

Sta-Lube Nickel Anti-Seize is a nickel based formula that is free of copper, lead, sulfides and chlorides. This premium quality lubricant has extremely high temperature and excellent chemical resistance.

**Product Specifications**

**Applications**

Catalyst beds, reaction chambers, special alloy fittings. May be used on fittings, bushings, flanges, headers, nuts, screws, studs, threaded surfaces, pipes, plugs, and manifolds to prevent seizing and galling of surfaces.

**Unit Package Description**

8 Ounce Brush-Top Bottle

**Brand**

Sta-Lube

**Generic Description 1**

General Purpose Anti Seize Lubricant

**Net Fill**

8 Wt Oz

**UPC Code**

0 72213 35911 4

**Unit Dimensions-Inches**

4.25H x 2.5W x 2.5D

**Units Per Case**

12

**Case Dimensions-Inches**

5H x 6.63W x 10D

**Cases Per Pallet**

108

**Lbs. Per Case**

8

**I 2 of 5 Code**

30072213359115

**Appearance**

Silver Semi-Solid Paste

**Odor**

Petroleum

**Base Type**

Nickel

**Flashpoint - TCC Method**

430°F

**Specific Gravity**

1.24

**Flammability**

Non-flammable

**Plastic Safe**

Yes

**Film Type**

Wet

**Evaporation Rate**

<0.01 (Butyl Acetate=1)

**Working Temp [Degrees F]**

-95 to 2400°F

**Propellant**

None

**NSF Registered**

No

**DOT Proper Shipping Name**

Not Regulated

**VOC % (Federal)**

0

**VOC g/L (Federal)**

0

**VOC Lbs./Gal. (Federal)**

0

**VOC Compliant For CA**

Not Regulated

**VOC Compliant For OTC/  
LADCO**

Not Regulated

**VOC Category/Limit**

Not Regulated

**Removal (How To)**

Remove with general purpose degreaser.

**SL35911 -- Nickel Anti-Seize Lubricating Compound, 8 Wt Oz**



**Product Description**

Sta-Lube Nickel Anti-Seize is a nickel based formula that is free of copper, lead, sulfides and chlorides. This premium quality lubricant has extremely high temperature and excellent chemical resistance.

**Product Specifications**

**Applications**

Catalyst beds, reaction chambers, special alloy fittings. May be used on fittings, bushings, flanges, headers, nuts, screws, studs, threaded surfaces, pipes, plugs, and manifolds to prevent seizing and galling of surfaces.

**Unit Package Description**

8 Ounce Brush-Top Bottle

**Brand**

Sta-Lube

**Generic Description 1**

General Purpose Anti Seize Lubricant

**Net Fill**

8 Wt Oz

**UPC Code**

0 72213 35911 4

**Unit Dimensions-Inches**

4.25H x 2.5W x 2.5D

**Units Per Case**

12

**Case Dimensions-Inches**

5H x 6.63W x 10D

**Cases Per Pallet**

108

**Lbs. Per Case**

8

**I 2 of 5 Code**

30072213359115

**Appearance**

Silver Semi-Solid Paste

**Odor**

Petroleum

**Base Type**

Nickel

**Flashpoint - TCC Method**

430°F

**Specific Gravity**

1.24

**Flammability**

Non-flammable

**Plastic Safe**

Yes

**Film Type**

Wet

**Evaporation Rate**

<0.01 (Butyl Acetate=1)

**Working Temp [Degrees F]**

-95 to 2400°F

**Propellant**

None

**NSF Registered**

No

**DOT Proper Shipping Name**

Not Regulated

**VOC % (Federal)**

0

**VOC g/L (Federal)**

0

**VOC Lbs./Gal. (Federal)**

0

**VOC Compliant For CA**

Not Regulated

**VOC Compliant For OTC/  
LADCO**

Not Regulated

**VOC Category/Limit**

Not Regulated

**Removal (How To)**

Remove with general purpose degreaser.